



**PANA-38DL PLUS-ACCY01**  
Accessory Kit

Part #	Description	Qty	
PANA-38DL PLUS-CASE01	Hard Case for PANA-38DL PLUS		
OLYM-2218E (Optional)	2218E Steel Test Block, 2 Step (0.050 & 1.500)		
GENE-PC-5-15A	Power Cord 120V 15A		
PANA-EP-MCA	AC Adapter, 24V 2.5A DC		
PANA-B2	Ultrasonic Couplant B, 2 oz		
PANA-38DL PLUS- MAN01	Operation Manual for PANA-38DL PLUS		






**PANA-38DL PLUS-ACCY01**  
Accessory Kit

Part #	Description	Qty	
PANA-38DL PLUS-STRAP01	Instrument Strap for PANA-38DL PLUS	1	
GENE-USB	USB Cable Type A to Type B, 6'	1	
PANA-38DL PLUS-MAN02	Getting Started Guide for PANA-38DL PLUS	1	
PANA-38DL PLUS-HOLSTER01	Rubber Holster with Hand Strap	1	
PANA-38DL PLUS-SW01	GageView Software CD	1	
PANA-38DL PLUS-BATTCLIP01	Alkaline Battery Clip for 38DL PLUS	1	



**PANA-38DL PLUS-ACCY01**  
Accessory Kit

Part #	Description	Qty	
PANA-D790-SM	5MHz Dual Element UltraSonic Transducer	1	
PANA-LCMD-316-5B	Dual MicroDot to Dual Lemo Transducer Cable for D790-SM	1	
OLYM-2214E	1018 Steel Test Block 5 Step	1	



**PANA-38DL PLUS-ACCY02**  
Accessory Kit

Part #	Description	Qty	
PANA-38DL PLUS-CASE01	Hard Case for PANA-38DL PLUS		
OLYM-2218E	2218E Steel Test Block, 2 Step (0.050 & 1.500)		
GENE-PC-5-15A	Power Cord 120V 15A		
PANA-EP-MCA	AC Adapter, 24V 2.5A DC		
PANA-B2	Ultrasonic Couplant B, 2 oz		
PANA-38DL PLUS- MAN01	Operation Manual for PANA-38DL PLUS		




**PANA-38DL PLUS-ACCY02**  
Accessory Kit

Part #	Description	Qty	
PANA-38DL PLUS-STRAP01	Instrument Strap for PANA-38DL PLUS	1	
GENE-USB	USB Cable Type A to Type B, 6'	1	
PANA-38DL PLUS-MAN02	Getting Started Guide for PANA-38DL PLUS	1	
PANA-38DL PLUS-HOLSTER01	Rubber Holster with Hand Strap	1	
PANA-38DL PLUS-SW01	GageView Software CD	1	
PANA-38DL PLUS-BATTCLIP01	Alkaline Battery Clip for 38DL PLUS	1	





**PANA-38DL PLUS-ACCY02**  
Accessory Kit

Part #	Description	Qty	
PANA-D790 or PANA-D790-SM	5MHz Dual Element UltraSonic Transducer	1	
PANA-LCMD-316-5B	Dual MicroDot to Dual Lemo Transducer Cable for D790-SM	1	