

Capacitive Coupling Clamp

CDN 8014 / CDN 8015

- Complies with IEC 61000-4-4
- Testing of peripheral interface ports

The coupling clamp is primarily used to inject fast transient and burst interference pulses into signal and data cables, i.e. into any type of connection to peripheral equipment.

The IEC standard 61000-4-4 also allows the capacitive coupling method to be used for pulse injection into ac and dc power lines when no appropriate decoupling network is available.

The coupling capacitance (typically 100pF) between the coupling clamp and the cable inserted depends on the cable type, the diameter and other factors like screening, etc.

The CDN 8014/8015 conforms to the standard in every respect.

It has a sturdy construction is suitable for laboratory and on-site use. The precision manufactured German silver coupling plates are housed in wooden case with a crystal-clear protective lid.

Contact plates on both sides of the case ensure the necessary grounding to the reference plane.

CDN 8015 with safety interlock facility

The CDN 8015 provides an interlock facility for safety purposes.

When used with any current Schaffner burst generator or BEST combination test generator, the coupling clamp interacts with the generator preventing the output of a high voltage pulses whilst the protective cover is open.



CDN 8015

Technical Specifications	CDN 8014 / 8015
Active coupling length	1m
Typical coupling capacitance between cable and clamp	50pF to 200pF
Cable diameter	up to 40mm
Max. Permissible burst voltage	8kV